


Stealth Retainer Sizing - String Measuring Method

- Gather Materials:
 - Approx 6" of String (included with Foam Sizing Guide)
 - Sharpie/Marker
 - Metric ruler or printed sizing guide (included with Sizing Foam Sizing Guide):
 Paper Sizing Guide V4 - Number Sizing.pdf
- While flaccid, wrap string around the glans at the "fitting circle" as shown below



- Mark where the end of the string meets after looping around the glans with a Sharpie
- Lay the String flat on the ruler, note the length indicated, below shows about 95mm



- Follow the recommendations for retainer size below:
 - Under 60mm = Size 8
 - 60 - 80mm = Size 10
 - 80 - 100mm = Size 12
 - 100 - 120mm = Size 14
 - Over 120mm = Size 16